


(4) Mounting Holes for M10 [3/8"] Screws



Note: Spreader bar required to avoid damage during lifting

Cooling fan location



Nameplate

Center of Gravity
Note: Dimensions shown are measured from the bottom left mounting hole



C/C: GA80□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
T208□□□	380 TO 480	60 (132.0)	2
T250□□□		61 (134.2)	2
T302□□□		62 (136.4)	2

□ denotes A-Z

YASKAWA



UNITS MM [IN]
SCALE 1:10

DRWN. J. MATTAS 1-11-21
CHKD. J. PIOTROWSKI 3-8-21
TECH. L. UDDIN 3-1-21
APRV. J. CAIRO 4-1-21

TITLE
GA800 12 PULSE DIMENSION DRAWING
FRAME SIZE 9
BACKSIDE TYPE 12 ENCLOSURE

SIZE A PAGE 1 OF 3
DWG.NO. DD.GA80.FR9.FLNG.12P

REV 0




C/C: GA80□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
T208□□□	R/L1, S/L2, T/L3	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
T250□□□	R1/L11, S1/L21, T1/L31	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
T302□□□	U, V, W	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
	-, +3	2 - 250 x 2P (35 - 120 x 2P)	M10	20 (177)
	⊕	2 - 350 (35 - 185)	M10	18 - 23 (159 - 204)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]

SCALE 1:8


DRWN.	J. MATTAS	1-11-21
CHKD.	J. PIOTROWSKI	3-8-21
TECH.	L. UDDIN	3-1-21
APRV.	J. CAIRO	4-1-21

TITLE	GA800 12 PULSE DIMENSION DRAWING FRAME SIZE 9 BACKSIDE TYPE 12 ENCLOSURE
-------	--

SIZE	A	PAGE	2 OF 3
DWG.NO.	DD.GA80.FR9.FLNG.12P		

REV
0


Panel Cutout



Notes:

Exposed heatsink minimum clearance D = 165 [6.50].
Refer to Type 12 heatsink external installation manual for additional details.

YASKAWA



UNITS MM [IN]

SCALE 1:8

DRWN.	J. MATTAS	1-11-21
CHKD.	J. PIOTROWSKI	3-8-21
TECH.	L. UDDIN	3-1-21
APRV.	J. CAIRO	4-1-21

TITLE	GA800 12 PULSE DIMENSION DRAWING FRAME SIZE 9 BACKSIDE TYPE 12 ENCLOSURE
-------	--

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.GA80.FR9.FLNG.12P		

REV
0