

注記：現在、システム機能の拡張が行われているため、データが欠落していたり、古いデータが表示されていたりする場合があります。この暫定期間中は、適合証明書を参照するか、カスタマーエクスペリエンスセンター (<https://www.ul.com/about/locations>) までお問い合わせください。

Power Conversion Equipment Certified for Canada - Component

COMPANY

Yaskawa America, Inc.

2121 Norman Dr S

Waukegan, IL 60085 United States

E147823

Marking: Company name or trademark  ,  , model designation, and the Recognized Component Mark for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

View model for additional information

AC Solid state servo drives, Model(s): [CACR-SR02@](#), [CACR-SR03@](#), [CACR-SR05@](#), [CACR-SR07@](#), [CACR-SR10@](#), [CACR-SR15@](#), [CACR-SR20@](#), [CACR-SR30@](#), [CACR-SR44@](#)

Alternating current solid state servo devices, Model(s): [SGDM](#) followed by 05, 10, 15, 20, 30, 50, 60, 75, 1A, or 1E, followed by AC, followed by SD1, may be followed by P or R, may be followed by Y8, 237 or 238.

Alternating current solid state servo devices, Model(s): [SGDM-01AC-SD2](#) may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): [SGDM-04AC-SD2](#) may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): [SGDM-04AC-SD2A](#) may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): [SGDM-04AC-SD2B](#) may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): [SGDM-05AC-SD2](#) may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): [SGDM-05AC-SD2A](#) may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): [SGDM-05AC-SD2B](#) may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): [SGDM-08AC-SD2](#) may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): SGDM-08AC-SD2A may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): SGDM-08AC-SD2B may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): SGDM-10AC-SD2 may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): SGDM-15AC-SD2 may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): SGDM-20AC-SD2 may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): SGDM-20AC-SD2A may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): SGDM-20AC-SD2B may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): SGDM-30AC-SD2 may be followed by P or R, may be followed by Y8, 237 or 238

Alternating current solid state servo devices, Model(s): SGDM-30AC-SD2A may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): SGDM-30AC-SD2B may be followed by P or R, may be followed by Y8, 237, 238 or M

Alternating current solid state servo devices, Model(s): SGDM-A3AC-SD2 may be followed by P or R, may be followed by Y8, 237 or 238

Open type, alternating current, solid state, servo drives, Model(s): SGDV followed by R70, R90, 1R6, 2R1, 2R8, 3R8, 5R5, 7R6, 1R9, 3R5, 5R4, A5, 01, 02, 04, 05, 08, 10, 15, or 120, followed by A, D or F, followed by two Alphanumeric characters, followed by A, may be followed by - and two alphanumeric characters, may be followed by three alphanumeric characters, may be followed two alphanumeric characters, may be followed by one alphanumeric character.

Open type, alternating current, solid state, servo drives, Model(s): SGDW followed by R70, R90, 1R6, 2R8 or 5R5, followed by A, followed by two alphanumeric characters, followed by A, may be followed by three alphanumeric characters, may be followed two alphanumeric characters, may be followed by one alphanumeric character.

Open type, direct current, solid state, servo drives, Model(s): SGDV followed by 1R7 or 2R9, followed by E, followed by two alphanumeric characters, followed by A, may be followed by three alphanumeric characters, may be followed two alphanumeric characters, may be followed by one alphanumeric character.

Open type, Industrial, AC Drive, Model(s): SGPMS followed by 1R5, 2R5, 4R0, 6R0, or 9R0, followed by A, followed by P0, 10, 30, or A0, followed by A or B, may be followed by Y, may be followed by up to five alphanumeric characters.

Open type, Industrial, AC Drive, Model(s): SGPMS-1R5A followed by P0, 10, 30, or A0, followed by A or B, may be followed by three alphanumeric characters

Open type, Industrial, AC Drive, Model(s): SGPMS-2R5A followed by P0, 10, 30, or A0, followed by A or B, may be followed by three alphanumeric characters

Open type, Industrial, AC Drive, Model(s): SGPMS-4R0A followed by P0, 10, 30, or A0, followed by A or B, may be followed by three alphanumeric characters

Open type, Industrial, AC Drive, Model(s): SGPMS-6R0A followed by P0, 10, 30, or A0, followed by A or B, may be followed by three alphanumeric characters

Open type, Industrial, AC Drive, Model(s): SGPMS-9R0A followed by P0, 10, 30, or A0, followed by A or B, may be followed by three alphanumeric characters

Open type, Industrial, DC Drive, Model(s): SGD7M followed by -D, followed by 3, followed by 0, followed by 0, followed by A, followed by 2, followed by B, followed by Y plus up to 5 alphanumeric characters.

Open type, Industrial, DC Drive, Model(s): SGD7M-D300A2B may be followed by up to three alphanumeric characters, may be followed by up to 4 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, Model(s): CACP-JU15 followed by A3B, CACP-JU37 followed by A3B

Open type, Modular, alternating current, solid state, servo/spindle drives, Model(s): CACP-JU19 followed by A3B may be followed by blank or B followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, Model(s): CACP-JU22 followed by A3B may be followed by blank or B followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, Model(s): CACP-JU30 followed by A3B may be followed by blank or B followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, Model(s): CACP-JU45 followed by A3B may be followed by blank or B followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, Model(s): CACR-JU followed by 014, 018, 033, 042, 051 or 98, followed by D, followed by 0, 2, C, D or E, followed by A or B, may be followed by B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, 1 - Axis drive, Model(s): CACR-JU014D followed by 0, 2, C, D or E, followed by A or B, may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, 1 - Axis drive, Model(s): CACR-JU018D followed by 0, 2, C, D or E, followed by A or B, may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, 1 - Axis drive, Model(s): CACR-JU033D followed by 0, 2, C, D or E, followed by A or B, may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, 1 - Axis drive, Model(s): CACR-JU042D followed by 0, 2, C, D or E, followed by A or B, may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, 1 - Axis drive, Model(s): CACR-JU051D followed by 0, 2, C, D or E, followed by A or B, may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, 1 - Axis drive, Model(s): CACR-JU98D followed by 0, 2, C, D or E, followed by A or B, may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, converter, Model(s): CACP-JU15 followed by D3B, may be followed by B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, converter, Model(s): CACP-JU15A3B may be followed by blank or B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, converter, Model(s): CACP-JU15D3B may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, converter, Model(s): CACP-JU19 followed by D3B, may be followed by B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter 1-axis drive, Model(s): CACR-JU028A followed by 0, 2, C, D or E, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter 1-axis drive, Model(s): CACR-JU036A followed by 0, 2, C, D or E, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter 1-axis drive, Model(s): CACR-JU065A followed by 0, 2, C, D or E, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter 1-axis drive, Model(s): CACR-JU084A followed by 0, 2, C, D or E, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter 1-axis drive, Model(s): CACR-JU102A followed by 0, 2, C, D or E, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter 1-axis drive, Model(s): CACR-JU125A followed by 0, 2, C, D or E, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter 1-axis drive, Model(s): CACR-JU196A followed by 0, 2, C, D or E, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter multi-axis, Model(s): CACR-JUM2 followed by 3, 4 or 5 followed by A or B followed by 0, 2 or C, followed by A, followed by blank or B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, inverter multi-axis, Model(s): CACR-JUM2 followed by 3, 4 or 5, followed by A followed by 0, 2 or C, followed by A or B, followed by blank or B, followed by Y with up to 5 alphanumeric characters

Open type, Modular, alternating current, solid state, servo/spindle drives, multi-axis, Model(s): CACR-JUM2 followed by 3, 4 or 5, followed by D, followed by 0, 2, or C, followed by A or B, may be followed by B, may be followed by two alphanumeric characters, may be followed by two alphanumeric characters, may be followed by one alphanumeric character

Open type, Modular, alternating current, solid state, servo/spindle drives, multi-axis, Model(s): CACR-JUM2 followed by 3, 4 or 5 followed by D, followed by 0, 2, or C, followed by A or B, may be followed by B, followed by Y with up to 5 alphanumeric characters

Open Type, Multi-winding Motor Controller Unit, Model(s): JUSP followed by -MD, followed by 1, 2, 3, 4 or 5, followed by A, followed by 01 or 11, followed by A, followed by 6 alphanumeric characters

Open type, solid state, servo drives, Model(s): CACR-01EX6A2-MI, CACR-0401IS3-FK, CACR-0401IS4-FK, CACR-0401IS6-FK, CACR-0410IS3-FK, CACR-0410IS4-FK, CACR-0410IS6-FK, SGDZ-BS51AN7A-FK, SGDZ-BS51AN7A-FK-E, SGDZ-BS60AN7A-FK, SGDZ-BS60AN7A-FK-E, SGDZ-BS61AN7A-FK, SGDZ-BS61AN7A-FK-E, SGDZ-BS62AN7A-FK, SGDZ-BS62AN7A-FK-E, SGDZ-BS63AN7A-FK-E, SGDZ-BS80AN7A-FK-E, SJDE-01ANA, SJDE-01APA, SJDE-01APA-OY, SJDE-02ANA, SJDE-02APA, SJDE-02APA-OY, SJDE-04ANA, SJDE-04APA, SJDE-04APA-OY, SJDE-08ANA, SJDE-08APA, SJDE-08APA-OY

Open type, solid state, servo drives, "Sigma 5-MD", Model(s): SGDV-MD followed by A01E or A02E, followed by 4, 8 or C, followed by M3, SQ, or EC, followed by A, may be followed by 01 or 02, may be followed by Y plus 1 to 4 alpha numeric characters.

Power Conversion Equipment, Model(s): ESVB-B510SAAB-SE, ESVB-B510SAAC-SE, JUSP-ECM07A, may be followed by 200, PMD-U-MP331S4C001, SGD7M-B510SAAA-TE, SGD7M-C200CA2A-FK, SGDZ-BS81AN2B-FK-E

Power Conversion Equipment, Model(s): SGD7M-C40LA3A may be followed by 0 or 2, may be followed by E, F, or 0, may be followed by two alphanumeric characters, may be followed by B

Regenerative Unit, "Sigma 5", Model(s): Models JUSP-RG010 followed by CA or EA

Servopacks, Model(s): SGDF followed by -A1, -A2, -A3, -B3, -B5 or -B9, followed by C, followed by S or P, may be followed by Y, may be followed by 1 to 3 digits.

@ - May be followed by additional letters and numbers.

@ - May be followed by additional numbers or letters

このデータベースに企業名や製品が掲載されている場合でも、掲載された製品がULのフォローアップサービスに基づいて製造されたことを保証するものではありません。ULの認証並びにフォローアップサービスによる確認を受けているとみなされるのは、ULマークが表示された製品のみです。常に製品にULマークが表示されているかご確認ください。

オンライン認証製品ディレクトリーに掲載される資料の転載は、以下の条件を満たす場合にのみ認められます。1.ガイド・インフォメーション（製品カテゴリーガイド）、アセンブリ、構造、設計、システム、および/または認証に関する情報（ファイル）が、誤解を招かない方法で、データや図面の変更を一切行うことなく、そのまま掲載されていること。2.転載された資料に隣接して、「Reprinted from the Online Certifications Directory with permission from UL」（ULの許可を得た上で、オンライン認証製品ディレクトリーから転載）」と記載すること。転載する資料には、著作権に関して次の形式で記載すること。"©2024 UL LLC."